



Main

Range of product	9007
Series name	Heavy duty
Product or Component Type	Limit switch head
Device short name	9007C
Head type	Plunger head
Product Compatibility	9007C
Associated lever	9007C
Associated body	9007C
Movement of operating head	Linear
Type of operator	Spring return roller plunger steel -
Type of approach	Lateral approach, 2 directions
Positive opening	Without

Complementary

Switch actuation	By 30° cam
Product Weight	0.25 lb(US) (0.11 kg)

Environment

Ambient Air Temperature for Operation	0...185 °F (-18...85 °C)
Ambient Air Temperature for Storage	0...185 °F (-18...85 °C)
Environmental characteristic	Standard environment

Ordering and shipping details

Category	21499 - 9007 C LIMIT SWITCHES
Discount Schedule	DS1
GTIN	00785901500810
Nbr. of units in pkg.	1
Package weight(Lbs)	4.16 oz (117.9 g)
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.69 in (4.3 cm)
Package 1 width	1.89 in (4.8 cm)
Package 1 Length	2.99 in (7.6 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[9007D](#)