



Main

Device short name	C
Enclosure type	Dust and damp proof weatherproof enclosure indoor/outdoor
Product Specific Application	Condensation pump
Switch application	Standard

Complementary

Electrical Connection	Screw clamp terminal
Float movement	4.75...9.25 in
Float position	Left
Material	Stainless steel float/rod Nitrile (Buna-N) seal ring
Maximum Horse Power Rating	3 Hp 115 V AC, 3 phase 2 Hp 115 V AC, 1 phase 3 Hp 230 V AC, 1 phase 5 Hp 230 V AC, 3 phase 1 hp 460/575 V AC, 3 phase
Mounting Support	Flange
Number of poles	2
Permissible voltage	575 V AC
Switch Function	DPST

Environment

NEMA Degree of Protection	NEMA 4
---------------------------	--------

Ordering and shipping details

Category	21601-9037,9038 COMMERCIAL FLOAT SWITCHES
Discount Schedule	CP7G
GTIN	785901934141
Nbr. of units in pkg.	1
Package weight(Lbs)	21 lb(US) (9.53 kg)
Returnability	No
Country of origin	MX

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
EU RoHS Directive	Not applicable, out of EU RoHS legal scope

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[9038CW36N4](#)