

## Product data sheet

### Characteristics

# 9050JCK28PTV14

Timing Relay, Type JCK, plug In, off delay power trigger, adjustable time, 0.6 to 60 minutes, 10A, 240 VAC, 24 VAC/DC



### Main

Product range	9050JCK
Product type	Timer
Timing mode	Off-delay power trigger
Timing range	0.6...60 min
Supply voltage	24 V AC/DC

### Complementary

Power consumption	2 VA
Current rating	10 A
Switch function	DPDT
Contact composition	2 NO + 2 NC
Contact material	Silver nickel
Maximum switching voltage	240 V AC
Mounting type	Socket
Number of pins	11
Shape of pins	Tubular
For use with	8501NR62 8501NR61

### Environment

Certifications	CSA UL Listed CE UL Recognized
Ambient temperature range - operational	-18...150 °F (-28...66 °C)
Height	2.40 in (61 mm)
Width	1.69 in (43 mm)
Depth	4.09 in (104 mm)

### Ordering and shipping details

Category	21651 - 9050 JCK(NOT JCK60, 70) G P TIMERS
Discount Schedule	CP2
GTIN	00785901960393
Nbr. of units in pkg.	5
Package weight(Lbs)	5 lb(US) (2.27 kg)
Returnability	No
Country of origin	US

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>

## Contractual warranty

Warranty	18 months
----------	-----------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[9050JCK28PTV14](#)