

# Product data sheet

## Characteristics

# ACAC20002

## CDU Flexible Fluid Piping - 300 Feet (91.4 Meters)



### Overview

Lead time	Usually Ships within 4 Weeks
-----------	------------------------------

### General

Provided Equipment	Installation guide
Maximum Recommended Flow Rate	18.5 gal(US)/min (1.17 l/s)
Piping Material	PEX-AL-PEX
Pressure Rating	150 psi (1034.21 kPa)
Fluid connection type	Unterminated
Minimum bending radius	8 in (203.20 mm)
Minimum Fluid Temperature	42 °F (6 °C)
Maximum Fluid Temperature	60 °F (16 °C)
Pressure Drop per foot (0.305m)	0.13 ft of water/ft 13.95 gal(US)/min (0.88 l/s)

### Physical

Length	300 ft (91.44 m)
Color	White
Depth	42.01 in (106.7 cm)
Height	10.98 in (27.9 cm)
Product Weight	83.18 lb(US) (37.73 kg)
Width	42.01 in (106.7 cm)


### Ordering and shipping details

GTIN	00731304241621
Package weight(Lbs)	87.19 lb(US) (39.55 kg)

### Packing Units

Package 1 Height	12.52 in (31.8 cm)
Package 1 width	45.51 in (115.6 cm)
Package 1 Length	45.51 in (115.6 cm)
Number of Units in Package 3	6

### Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
-------------------	--

Contractual warranty

Warranty	1 year (parts only)
----------	---------------------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[ACAC20002](#)