



Overview

Lead time	Special Order - Call for Quoted Lead Times
-----------	--

Main

Main Input Voltage	208 V 230 V
Number of rack unit	42U
Provided Equipment	Installation guide Operations and maintenance manual

General

Compressor Type	Scroll
Air Discharge Patterns	Horizontal
Intake Air	Rear Return
Refrigerant Charge	5 lb(US) (2.27 kg)
Air flow	2290 ft³/min (1080.76 l/s)
Condensate Pump Capacity	2.6 Gal/hr(US) (0.01 m³/h)

Physical

Color	Black
Height	78.39 in (199.1 cm)
Width	11.81 in (30 cm)
Depth	42.13 in (107 cm)
Net Weight	438.92 lb(US) (199.09 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Input

Input power	4600 W
Input Frequency	60 Hz

Conformance

Product Certifications	CUL Listed C-tick CE UL Listed
------------------------	---

Communications & Management

Control panel	Multi-function LCD status and control console
Audible Alarm	Audible and visible alarms prioritized by severity

Ordering and shipping details

GTIN	731304264453
Package weight(Lbs)	523.09 lb(US) (237.27 kg)

Packing Units

Package 1 Height	83.39 in (211.8 cm)
Package 1 width	29.37 in (74.6 cm)
Package 1 Length	44.76 in (113.7 cm)
Number of Units in Package 3	1

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Not applicable, out of EU RoHS legal scope

Contractual warranty

Warranty	1 year (parts only), 1 year on-site repair or replace with factory authorized Start-Up
----------	--

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[ACRD200](#)