

Main

Product or Component Type	Cable duct
Accessory / separate part category	Cabling accessories
Range compatibility	S3D CRN PLA PLS PLM
Device Composition	Without cover
Quantity per Set	Set of 8

Complementary

Color	Gray RAL 7030)
Fixing Mode	By screws Clip-on support
Material	PVC (polyvinyl chloride)
Height	2.95 in (75 mm)
Length	78.74 in (2000 mm)
Width	2.95 in (75 mm)
Net Weight	2.29 lb(US) (1.04 kg)
Total number of wires	400

Environment

Ambient Air Temperature for Operation	23...140 °F (-5...60 °C)
Flame retardance	V-0 UL 94
Fire resistance	1760 °F (960 °C) IEC 60695-2-1/1
Standards	VDE 0506 DIN 43659 VDE 0660

Ordering and shipping details



Category	22622-PANEL BUS_(OLD STYLE)
Discount Schedule	I
GTIN	3389110570472
Nbr. of units in pkg.	1
Package weight(Lbs)	2.39 lb(US) (1.084 kg)
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	5.71 in (14.5 cm)
Package 1 width	6.30 in (16 cm)
Package 1 Length	8.27 in (21 cm)
Unit Type of Package 2	PAL
Number of Units in Package 2	320
Package 2 Weight	791.46 lb(US) (359.0 kg)

Package 2 Height	44.69 in (113.5 cm)
Package 2 width	35.43 in (90 cm)
Package 2 Length	82.68 in (210 cm)
Unit Type of Package 3	CAR
Number of Units in Package 3	8
Package 3 Weight	19.14 lb(US) (8.68 kg)
Package 3 Height	5.71 in (14.5 cm)
Package 3 width	6.30 in (16 cm)
Package 3 Length	82.68 in (210 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[AK2GD7575](#)