



### Main

Range	Linergy
Product name	HK
Product or Component Type	Mounting plate
Poles description	1P + N
[I <sub>th</sub> ] conventional free air thermal current	25 A
I <sup>2</sup> t on activation	200000 A <sup>2</sup> .s
Number of cables	2 0.01 in <sup>2</sup> (4 mm <sup>2</sup> ) 221 °F (105 °C)
Width	2.13 in (54 mm)
Height	4.13 in (105 mm)
Depth	2.40 in (61 mm)

### Complementary

[Ui] rated insulation voltage	690 V IEC 60439-1
9 mm pitches	6
Net Weight	0.30 lb(US) (0.135 kg)

### Environment

Standards	IEC 60439
Product Certifications	LROS (Lloyds register of shipping) UL CSA DNV



### Ordering and shipping details

Category	22623-PANEL BUS (AK5)
Discount Schedule	I11
GTIN	3389110537420
Nbr. of units in pkg.	1
Package weight(Lbs)	7.34 oz (208.0 g)
Returnability	No
Country of origin	FR

### Packing Units

Unit Type of Package 1	PCE
Package 1 Height	2.48 in (6.3 cm)
Package 1 width	2.87 in (7.3 cm)
Package 1 Length	4.72 in (12 cm)

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes

RoHS exemption information	 <a href="#">Yes</a>
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

### Contractual warranty

Warranty	18 months
----------	-----------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[AK5PA211N3](#)