

Product availability: Stock - Normally stocked in distribution facility



Main

Range	Linergy
Product name	HK
Product or component type	Mounting plate
Poles description	2P
[I _{th}] conventional free air thermal current	25 A
I ² t on activation	200000 A ² .s
Number of cables	2 cable(s) 0.01 in ² (4 mm ²) at 221 °F (105 °C)
Width	2.13 in (54 mm)
Height	4.13 in (105 mm)
Depth	2.4 in (61 mm)

Complementary

[Ui] rated insulation voltage	690 V conforming to IEC 60439-1
9 mm pitches	6
Product weight	0.3 lb(US) (0.135 kg)

Environment

Standards	IEC 60439
Product certifications	DNV LR0S (Lloyds register of shipping) UL CSA

Ordering and shipping details

Category	22623 - PANEL BUS (AK5)
Discount Schedule	I11
GTIN	00785901787266
Nbr. of units in pkg.	1
Package weight(Lbs)	0.5200000000000002
Returnability	Y
Country of origin	FR

Contractual warranty

Warranty period	18 months
-----------------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[AK5PA211PH12](#)