



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Main Input Voltage	230 V
Main Output Voltage	230 V
Plug standard	IEC 60309 32 A 2P+E
Number of rack unit	2U
Cable length	8 ft (2.44 m)
Number of cables	2
Provided Equipment	Rack Mounting brackets RS-232 configuration cable Serial configuration cable

Physical

Color	Black
Height	3.46 in (8.8 cm)
Width	17.01 in (43.2 cm)
Depth	9.29 in (23.6 cm)
Net Weight	15.30 lb(US) (6.94 kg)
Mounting Location	Front Rear
Mounting preference	No preference
Mounting Mode	Rack-mounted

Input

Input Frequency	50/60 Hz
Max line current	32 A
Input current limits	32 A
Load Capacity	7400 VA

Output

Maximum Total Current Draw per Phase	32 A
Number of power socket outlets	16 IEC 60320 C13 2 IEC 60320 C19
Protection Type	Circuit breaker

Conformance

Standards	EN 55022 Class A FCC Part 15 class A
-----------	---

Environmental

Ambient Air Temperature for Operation	23...113 °F (-5...45 °C)
Relative Humidity	5...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	5...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)




Ordering and shipping details

GTIN	731304333432
Package weight(Lbs)	20.79 lb(US) (9.43 kg)

Packing Units

Package 1 Height	8.27 in (21 cm)
Package 1 width	22.99 in (58.4 cm)
Package 1 Length	14.02 in (35.6 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Lead free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[AP4424](#)