



### Overview

Lead time	Usually in Stock
-----------	------------------



### Main

Main Input Voltage	3 phase
Main Output Voltage	200 V 208 V
Number of rack unit	1U
Cable length	8 ft (2.44 m)
Provided Equipment	Installation guide Rack Mounting brackets

### Physical

Color	Black
Height	1.73 in (4.4 cm)
Width	17.20 in (43.7 cm)
Depth	10.00 in (25.4 cm)
Net Weight	17.59 lb(US) (7.98 kg)
Mounting Location	Front Rear
Mounting preference	No preference
Mounting Mode	Rack-mounted

### Input

Line Rated Current	40 A
Input current limits	50 A
Load Capacity	14400 VA
Input Frequency	50/60 Hz
Number of input connectors	1 CS8365

### Output

Number of power socket outlets	6 IEC 60320 C19
--------------------------------	-----------------

## Conformance

Product Certifications	CUL Listed METI Denan UL Listed
Standards	CSA C22.2 No. 60950-1-03 UL 60950-1

## Environmental

Ambient Air Temperature for Operation	23...113 °F (-5...45 °C)
Relative Humidity	5...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	5...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)



## Ordering and shipping details

GTIN	731304232674
Package weight(Lbs)	22.27 lb(US) (10.1 kg)

## Packing Units

Package 1 Height	9.49 in (24.1 cm)
Package 1 width	22.01 in (55.9 cm)
Package 1 Length	19.76 in (50.2 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Lead free	Yes
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[AP7516](#)