



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Main Input Voltage	200 V 208 V 230 V
Main Output Voltage	208 V
Input Connection Type	NEMA L6-20P
Number of rack unit	0U
Cable length	10 ft (3.05 m)
Number of cables	1
Provided Equipment	Installation guide Rack Mounting brackets Toolless Mounting Kit

Physical

Color	Black
Height	63.74 in (161.9 cm)
Width	2.20 in (5.6 cm)
Depth	1.73 in (4.4 cm)
Net Weight	10.71 lb(US) (4.86 kg)
Mounting Location	Side
Mounting preference	No preference
Mounting Mode	Rack-mounted

Input

Line Rated Current	16 A
Input current limits	20 A
Load Capacity	3300 VA
Input Frequency	50/60 Hz

Output

Number of power socket outlets	20 IEC 60320 C13 4 IEC 60320 C19
--------------------------------	-------------------------------------

Conformance

Product Certifications	CUL Listed UL Listed
Standards	CSA C22.2 No. 60950-1-03 UL 60950-1

Environmental

Ambient Air Temperature for Operation	32...113 °F (0...45 °C)
Relative Humidity	5...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	5...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)



Ordering and shipping details

GTIN	731304207931
Package weight(Lbs)	12.72 lb(US) (5.77 kg)

Packing Units

Package 1 Height	84.02 in (213.4 cm)
Package 1 width	5.98 in (15.2 cm)
Package 1 Length	5.00 in (12.7 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Lead free	Yes
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[AP7540](#)