



Overview

Lead time	Usually in Stock
-----------	------------------

General

Provided Equipment	Cord retention bracket(s) Documentation CD Installation guide Rack Mounting brackets Toolless Mounting Kit
--------------------	--

Physical

Cable length	3 ft (0.91 m)
Color	Black
Depth	3.50 in (8.9 cm)
Height	70.00 in (177.8 cm)
Product Weight	15.32 lb(US) (6.95 kg)
Width	2.20 in (5.6 cm)

Input

Max line current	35 A
Input current limits	35 A
Load Capacity	12500 VA
Input Frequency	50/60 Hz
Number of input connectors	1 CS8365
Nominal Input Voltage	3 phase

Output

Number of power socket outlets	30 IEC 60320 C13 6 IEC 60320 C19
--------------------------------	-------------------------------------

Conformance

Product Certifications	CUL Listed UL Listed
Standards	CSA C22.2 No. 60950-1-03 UL 60950-1

Environmental

Ambient Air Temperature for Operation	23...113 °F (-5...45 °C)
Relative Humidity	5...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	5...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)



Ordering and shipping details

GTIN	00731304226833
Package weight(Lbs)	22.42 lb(US) (10.17 kg)

Packing Units

Package 1 Height	82.99 in (210.8 cm)
Package 1 width	5.98 in (15.2 cm)
Package 1 Length	5.00 in (12.7 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Lead free	Yes
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[AP7568](#)