



Overview

Lead time	Usually in Stock
-----------	------------------



Main

Main Input Voltage	200 V 208 V
Main Output Voltage	208 V
Plug standard	NEMA L14-30P
Number of rack unit	2U
Cable length	28 ft (8.53 m)
Number of cables	1
Provided Equipment	Installation guide Rack Mounting brackets

Physical

Color	Black
Height	3.50 in (8.9 cm)
Width	17.20 in (43.7 cm)
Depth	3.50 in (8.9 cm)
Net Weight	14.02 lb(US) (6.36 kg)
Mounting Location	Front Rear
Mounting preference	Lower
Mounting Mode	Rack-mounted

Input

Line Rated Current	24 A
Input current limits	30 A
Load Capacity	4992 VA
Input Frequency	50/60 Hz

Output

Number of power socket outlets	4 NEMA L6-30R
--------------------------------	---------------

Conformance

Product Certifications	CUL Listed METI Denan UL Listed
Standards	CSA C22.2 No. 107.1 UL 1778

Environmental

Ambient Air Temperature for Operation	32...113 °F (0...45 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Ordering and shipping details

GTIN	731304222569
Package weight(Lbs)	16.03 lb(US) (7.27 kg)

Packing Units

Package 1 Height	5.98 in (15.2 cm)
Package 1 width	20.51 in (52.1 cm)
Package 1 Length	20.51 in (52.1 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Lead free	Yes
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[AP7584](#)