



Overview

Lead time	Usually in Stock
-----------	------------------

General

Provided Equipment	Installation guide Rack Mounting brackets Toolless Mounting Kit
--------------------	---

Physical

Cable length	10 ft (3.05 m)
Color	Black
Depth	1.73 in (4.4 cm)
Height	70.00 in (177.8 cm)
Product Weight	12.28 lb(US) (5.57 kg)
Width	2.20 in (5.6 cm)

Input

Line Rated Current	16 A
Input current limits	20 A
Load Capacity	5700 VA
Input Frequency	50/60 Hz
Plug standard	NEMA L21-20P
Nominal Input Voltage	3 phase

Output

Number of power socket outlets	42 NEMA 5-20R
--------------------------------	---------------

Conformance

Product Certifications	CUL Listed UL Listed
Standards	CSA C22.2 No. 60950-1-03 UL 60950-1

Environmental

Ambient Air Temperature for Operation	32...113 °F (0...45 °C)
Relative Humidity	5...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	5...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Ordering and shipping details

GTIN	00731304223085
Package weight(Lbs)	19.53 lb(US) (8.86 kg)

Packing Units

Package 1 Height	84.02 in (213.4 cm)
Package 1 width	5.98 in (15.2 cm)
Package 1 Length	5.00 in (12.7 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Lead free	Yes
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[AP7592](#)