

Product data sheet

Characteristics

AP7750A

Rack ATS, 100-120V, 15A, 5-15P In, (10) 5-15R Out



Commercial status

This Product is Obsolete : DEC 02, 2020

 This Product is Obsolete

Overview

Lead time	Usually in Stock
-----------	------------------

General

Provided Equipment	Rack Mounting brackets User Manual
--------------------	---------------------------------------

Physical

Cable length	8 Ft (2.44 m)
Color	Black
Depth	9.29 In (23.6 cm)
Height	1.73 In (4.4 cm)
Product Weight	10.36 Lb(US) (4.7 kg)
Width	17.01 In (43.2 cm)

Input

Input Frequency	50/60 Hz
Line Rated Current	12 A
Plug standard	NEMA 5-15P
Permissible voltage	100...125 V
Input current limits	15 A
Load Capacity	1440 VA
Nominal Input Voltage	100 V 120 V

Output

Max current draw	15 A
Number of power socket outlets	10 NEMA 5-15R
Output voltage	100 V 120 V

Conformance

Product Certifications	PSE TÜV-C TÜV-NURTL VCCI Class A
Standards	FCC Part 15 class A ICES-003

Environmental

Ambient Air Temperature for Operation	23...113 °F (-5...45 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 Ft (0.00...15240.00 m)

Ordering and shipping details

GTIN	00731304299899
Package weight(Lbs)	14.29 Lb(US) (6.48 kg)

Packing Units

Package 1 Height	2.76 In (7 cm)
Package 1 width	19.13 In (48.6 cm)
Package 1 Length	13.50 In (34.3 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Lead free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Product Life Status : **Post commercialisation**

AP7750A may be replaced by any of the following products:



AP4450

Rack ATS, 100/120V, 15A, 5-15 in, (10) 5-15R out

Qty 1

Substitution date: | Migration SPD

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[AP7750A](#)