



### Overview

Presentation	This APC Switched Rack PDU power distribution unit has a wide range of standardized PDU features that increase network efficiency, manageability and functionality. The output and input connections are (8)5-15. Network management capabilities allow you to configure and manage rack PDUs from remote locations. It has a local current monitoring display that gives a visible warning in case of an overload. The remote individual outlet control provides real-time monitoring of connected loads. It has a multi-tier user access that enables you to restrict unauthorized use of outlets. This rack has a single input power source making it easy to install.
Lead time	Usually in Stock

### Main

Main Input Voltage	100 V 120 V
Main Output Voltage	120 V
Plug standard	NEMA 5-15P
Number of rack unit	1U
Cable length	12 ft (3.66 m)
Number of cables	1
Provided Equipment	Cord retention bracket(s) Horizontal mounting brackets User Manual Installation guide

### Physical

Color	Black
Height	1.73 in (4.4 cm)
Width	17.52 in (44.5 cm)
Depth	4.25 in (10.8 cm)
Net Weight	5.00 lb(US) (2.27 kg)
Mounting Location	Front Rear
Mounting preference	No preference
Mounting Mode	Rack-mounted

### Input

Line Rated Current	12 A
Acceptable Input Voltage	100...120 V
Input current limits	15 A
Load Capacity	1440 VA
Input Frequency	50/60 Hz

### Output

Number of power socket outlets	8 NEMA 5-15R
--------------------------------	--------------

## Conformance

Product Certifications	CUL Listed UL Listed
Standards	FCC Part 15 class A ICES-003

## Environmental

Ambient Air Temperature for Operation	32...113 °F (0...45 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

## Ordering and shipping details

GTIN	731304331568
Package weight(Lbs)	7.61 lb(US) (3.45 kg)

## Packing Units

Package 1 Height	2.76 in (7 cm)
Package 1 width	18.50 in (47 cm)
Package 1 Length	13.50 in (34.3 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[AP7900B](#)