



Overview

Lead time	Usually in Stock
-----------	------------------



Main

Main Input Voltage	200 V 208 V 230 V
Main Output Voltage	208 V
Input Connection Type	NEMA L6-30P
Number of rack unit	2U
Cable length	12 ft (3.66 m)
Number of cables	1
Provided Equipment	Documentation CD Installation guide Rack Mounting brackets

Physical

Color	Black
Height	3.50 in (8.9 cm)
Width	17.48 in (44.4 cm)
Depth	10.00 in (25.4 cm)
Net Weight	13.93 lb(US) (6.32 kg)
Mounting Location	Front Rear
Mounting preference	No preference
Mounting Mode	Rack-mounted

Input

Line Rated Current	24 A
Acceptable Input Voltage	200...240 V
Input current limits	30 A
Load Capacity	4992 VA
Input Frequency	50/60 Hz

Output

Number of power socket outlets	16 IEC 60320 C13
--------------------------------	------------------

Conformance

Product Certifications	CUL Listed CSA Industry Canada PSE UL Listed
Standards	FCC Part 15 class A ICES-003 UL 60950

Environmental

Ambient Air Temperature for Operation	32...113 °F (0...45 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)





Ordering and shipping details

GTIN	731304331605
Package weight(Lbs)	18.43 lb(US) (8.36 kg)

Packing Units

Package 1 Height	5.75 in (14.6 cm)
Package 1 width	20.24 in (51.4 cm)
Package 1 Length	20.24 in (51.4 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[AP7911B](#)