



Overview

Lead time	Special Order - Call for Quoted Lead Times
-----------	--

Physical

Cable length	2 ft (0.61 m)
Color	Black
Depth	2.56 in (6.5 cm)
Height	11.81 in (30 cm)
Product Weight	2.47 lb(US) (1.12 kg)
Width	2.36 in (6 cm)

Input

Plug standard	IEC 60320 C20
Number of cables	6
Max line current	16 A
Input current limits	16 A

Output

Max current draw	16 A
Number of power socket outlets	1 IEC 60320 C19
Cord Length	2 ft (0.61 m)

Conformance

Product Certifications	CCC CSA PSE UL Listed VDE
------------------------	---------------------------------------

Environmental

Ambient Air Temperature for Operation	32...167 °F (0...75 °C)
Relative Humidity	20...80 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...167 °F (-25...75 °C)
Storage Relative Humidity	20...80 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Ordering and shipping details

GTIN	00731304335597
Package weight(Lbs)	2.47 lb(US) (1.12 kg)

Packing Units

Package 1 Height	11.81 in (30 cm)
Package 1 width	2.36 in (6 cm)
Package 1 Length	2.56 in (6.5 cm)
Number of Units in Package 3	390

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[AP8712SX809](#)