



Overview

Lead time	Usually in Stock
-----------	------------------



Main

Main Input Voltage	100 V 120 V
Main Output Voltage	120 V
Plug standard	NEMA L5-30P
Number of rack unit	1U
Cable length	12 ft (3.66 m)
Number of cables	1
Provided Equipment	User Manual Rack Mounting brackets

Physical

Color	Black
Height	1.73 in (4.4 cm)
Width	17.60 in (44.7 cm)
Depth	2.24 in (5.7 cm)
Net Weight	5.51 lb(US) (2.5 kg)
Mounting Location	Front Rear
Mounting preference	No preference
Mounting Mode	Rack-mounted

Input

Line Rated Current	24 A
Acceptable Input Voltage	90...132 V
Max line current	24 A
Input current limits	30 A
Load Capacity	2880 VA
Input Frequency	50/60 Hz

Output

Number of power socket outlets	10 NEMA 5-20R
--------------------------------	---------------

Conformance

Product Certifications	CUL Listed UL Listed
Standards	UL 60950

Environmental

Ambient Air Temperature for Operation	5...113 °F (-15...45 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)



Ordering and shipping details

Category	11309-APC RESALE PRODUCTS
Discount Schedule	APC1
GTIN	731304192930
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	No
Country of origin	IN

Packing Units

Package 1 Height	5.98 in (15.2 cm)
Package 1 width	19.13 in (48.6 cm)
Package 1 Length	6.97 in (17.7 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Lead free	Yes
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[AP9560](#)