



Overview

Presentation	Rack PDU power cords for a variety of IT equipment. The output and input connections are C19 to C20. The cord length is 4.5m. The Nominal Output Voltage is 230V.
Lead time	Usually in Stock

Main

Main Output Voltage	230 V
Input Connection Type	IEC 60320 C20
Cable length	15 ft (4.57 m)
Number of cables	1

Physical

Color	Black
Net Weight	3.51 lb(US) (1.59 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Input

Acceptable Input Voltage	200...240 V
Input current limits	16 A

Output

Maximum Total Current Draw per Phase	16 A
Number of power socket outlets	1 IEC 60320 C19

Conformance

Product Certifications	VDE
------------------------	-----

Ordering and shipping details

Category	11309 - APC RESALE PRODUCTS
GTIN	731304204138
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	No
Country of origin	US

Packing Units

Package 1 Height	22.52 in (57.2 cm)
Package 1 width	18.50 in (47 cm)
Package 1 Length	4.49 in (11.4 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Lead free	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[AP9887](#)