



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Battery Type	Li-Ion (Lithium Ion)
Provided Equipment	Installation guide Reusable packaging

Physical

Color	Green Gray
Height	1.64 in (4.16 cm)
Width	3.05 in (7.74 cm)
Depth	6.00 in (15.23 cm)
Net Weight	1.28 lb(US) (0.58 kg)
Mounting Mode	Not rack-mountable

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Operating altitude	0...10000 ft
Relative Humidity	0...85 %
Ambient Air Temperature for Storage	-4...140 °F (-20...60 °C)
Storage altitude	0...50000 ft (0.00...15240.00 m)
Storage Relative Humidity	0...95 %

Batteries & Runtime

Battery Placement	Internal Battery
Battery Slots Empty	0
Included Battery Modules	0
RBC Quantity	1

Ordering and shipping details

GTIN	731304306139
Package weight(Lbs)	1.65 lb(US) (0.75 kg)

Packing Units

Package 1 Height	3.07 in (7.8 cm)
Package 1 width	5.12 in (13 cm)
Package 1 Length	8.15 in (20.7 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
Take-back	Take-back program available

Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[APCRBC146-LI](#)