



Overview

Lead time	Special Order - Call for Quoted Lead Times
-----------	--

Main

Number of rack unit	42U
Number of cables	1
Provided equipment	Doors Roof User Manual Key(s)

Physical

Color	Black
Height	81.50 in (207 cm)
Width	22.99 in (58.4 cm)
Depth	42.20 in (107.2 cm)
Net Weight	432.90 lb(US) (196.36 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable
Maximum Mounting Depth	36.77 in (93.4 cm)
Rack Width	19"
Marking	14 gauge EIA mounting rail 16 gauge front door 16 gauge post 16 gauge rear door 18 gauge roof
Permanent permissible load	1000 lb(US) (453.59 kg) static

Conformance

Standards	NEBS GR-63-CORE (Seismic Zone 4) EIA-310E
-----------	--




Ordering and shipping details

GTIN	731304205203
Package weight(Lbs)	471.00 lb(US) (213.64 kg)

Packing Units

Package 1 Height	87.01 in (221 cm)
Package 1 width	29.49 in (74.9 cm)
Package 1 Length	47.52 in (120.7 cm)
Number of Units in Package 3	1

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
Take-back	Take-back program available

Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[AR2145BLK](#)