



Overview

Presentation	Deep Universal IT Enclosure for low to medium density server and networking applications that either require additional equipment clearance space or more open space for ease of access in the rear of the enclosure. Compact width to optimize data center space. 42U height to easily roll through doorways.
Lead time	Usually in Stock

Main

Number of rack unit	42U
Provided equipment	Baying hardware Key(S) Keyed-alike doors and side panels Leveling feet Mounting Hardware Pre-installed casters Side Panels

Physical

Color	Black
Height	78.39 in (199.1 cm)
Width	23.62 in (60 cm)
Depth	47.24 in (120 cm)
Net Weight	295.62 lb(US) (134.09 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable
Maximum Mounting Depth	41.26 in (104.8 cm)
Minimum Mounting Depth	7.52 in (19.1 cm)
Rack Width	19"
Marking	14 gauge EIA mounting rail 16 gauge front door 16 gauge post 18 gauge rear door 18 gauge roof 18 gauge side panels
Permanent permissible load	2250 Lb(US) (1020.58 kg) dynamic 3750 lb(US) (1700.97 kg) static

Conformance

Standards	UL 2416 UL 60950-1 EIA-310E
-----------	-----------------------------------



Ordering and shipping details

GTIN	731304256274
Package weight(Lbs)	328.69 lb(US) (149.09 kg)

Packing Units

Package 1 Height	83.39 in (211.8 cm)
Package 1 width	29.61 in (75.2 cm)
Package 1 Length	52.52 in (133.4 cm)
Number of Units in Package 3	1

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
Take-back	Take-back program available

Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[AR3300](#)