



Overview

Lead time	Special Order - Call for Quoted Lead Times
-----------	--

General

Provided equipment	Baying hardware Documentation CD Key(S) Leveling feet Mounting Hardware Pre-installed casters Side Panels User Manual
--------------------	--

Physical

Maximum Mounting Depth	41.26 in (104.8 cm)
Number of rack unit	48U
Minimum Mounting Depth	10.31 in (26.19 cm)
Marking	14 gauge EIA mounting rail 16 gauge front door 16 gauge post 16 gauge rear door 18 gauge roof 18 gauge side panels
Color	Black
Depth	47.24 in (120 cm)
Rack width	19"
Height	109.88 in (279.1 cm)
Product Weight	485.02 lb(US) (220 kg)
Permanent permissible load	2250 Lb(US) (1020.58 kg) dynamic 3000 lb(US) (1360.78 kg) static
Width	29.53 in (75 cm)

Conformance

Standards	UL 60950 EIA-310E
-----------	----------------------

Ordering and shipping details

Package weight(Lbs)	553.36 lb(US) (251 kg)
---------------------	------------------------

Packing Units

Package 1 Height	115.98 in (294.6 cm)
Package 1 width	35.24 in (89.5 cm)
Package 1 Length	52.52 in (133.4 cm)
Number of Units in Package 3	1

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Lead free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
Take-back	Take-back program available

Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[AR3357X790](#)