



Overview

Lead time	Special Order - Call for Quoted Lead Times
-----------	--

General

Provided equipment	Baying hardware Key(S) Keyed-alike doors and side panels Leveling feet Mounting Hardware Pre-installed casters Side Panels User Manual
--------------------	---

Physical

Maximum Mounting Depth	41.26 in (104.8 cm)
Number of rack unit	45U
Minimum Mounting Depth	10.31 in (26.19 cm)
Marking	14 gauge EIA mounting rail 16 gauge front door 16 gauge post 18 gauge rear door 18 gauge roof 18 gauge side panels
Color	Black
Depth	47.24 in (120 cm)
Rack width	19"
Height	83.62 in (212.4 cm)
Product Weight	395.00 lb(US) (179.17 kg)
Permanent permissible load	2250 Lb(US) (1020.58 kg) dynamic 3000 lb(US) (1360.78 kg) static
Width	31.50 in (80 cm)

Conformance

Standards	UL 2416 UL 60950-1 EIA-310E
-----------	-----------------------------------



Ordering and shipping details

GTIN	00731304329329
Package weight(Lbs)	429.99 lb(US) (195.04 kg)

Packing Units

Package 1 Height	88.19 in (224 cm)
Package 1 width	37.40 in (95 cm)
Package 1 Length	52.52 in (133.4 cm)
Number of Units in Package 3	1

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[AR3385X266](#)