

C2

APC AV C Type 2 Outlet Wall Mount Power Filter, 120V



Overview

Lead time	Usually in Stock
-----------	------------------

General

Provided equipment	Detachable power cord User Manual Wall-mounting template
--------------------	--

Physical

Color	Black
Cable length	2 ft (0.61 m)
Depth	1.61 in (4.1 cm)
Height	3.70 in (9.4 cm)
Product Weight	1.50 lb(US) (0.68 kg)
Width	6.69 in (17 cm)

Input

Input Frequency	50/60 Hz
Switching current capacity	15 A
Nominal Input Voltage	120 V
Maximum Input Current per Phase	12 A
Plug standard	NEMA 5-15P

Output

Number of power socket outlets	2
Outlet standard	NEMA 5-15R

Conformance

Product Certifications	CUL Listed NOM
Standards	FCC part 68 UL 1363 UL 1449
Equipment protection policy	Lifetime : \$350000
UL 1449 TVSS Rating	400

Environmental

Ambient Air Temperature for Operation	32...122 °F (0...50 °C)
Operating altitude	0...10000 ft
Relative Humidity	0...95 %
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage altitude	0...50000 ft (0.00...15240.00 m)
Storage Relative Humidity	0...95 %

Surge Protection and Filtering

Let Through Voltage Rating	40 V
NM Surge Response Time (ns)	0 ns common mode
Common mode rejection	55 dB
Surge energy rating	1890 J

Ordering and shipping details

Category	11309 - APC RESALE PRODUCTS
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	No
Country of origin	PH

Packing Units

Package 1 Height	10.00 in (25.4 cm)
Package 1 width	7.99 in (20.3 cm)
Package 1 Length	1.50 in (3.8 cm)
SCC14	10731304248849
Number of Units in Package 2	3
Package 2 Weight	7.26 lb(US) (3.29 kg)
Package 2 Height	10.25 in (260.35 mm)
Package 2 width	8.6 in (218.44 mm)
Package 2 Length	5 in (127.00 mm)
Number of Units in Package 3	360

Offer Sustainability

EU RoHS Directive	Under investigation
Mercury free	Yes
RoHS exemption information	 Yes

Contractual warranty

Warranty	Lifetime
----------	----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[C2](#)