

Product data sheet

Characteristics

TSXCANCADD5

CANopen cordset - molded female SUB-D9 connectors - standard - IP20 - 5 m

Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Range of product	CANopen
Bus type	CANopen
Accessory / separate part category	Connection accessories
Accessory / separate part type	Connecting cable
Accessory / separate part destination	CANopen bus
Cable length	16.4 ft (5 m)

Complementary

Electrical connection	2 female connectors SUB-D 9 pin(s)
Marking	CE
Product weight	0.97 lb(US) (0.44 kg)

Environment

IP degree of protection	IP20
-------------------------	------

Ordering and shipping details

Category	22531 - PLCS, TWIDO, TWD
Discount Schedule	PC12
GTIN	003595863860184
Nbr. of units in pkg.	1
Package weight(Lbs)	0.9699999999999999
Returnability	N
Country of origin	PT

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1005 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[TSXCANCADD5](#)