



### Main

Range	D10S
Product	Disconnect Switch
Current Rating	100 A
Horsepower Rating	15 Hp 120 V AC 30 Hp 200/240 V AC 60 Hp 480 V AC 75 hp 600 V AC
Voltage Rating	600 V AC
Mounting Type	Door
NEMA Size	3
Service Entrance Rated	Service entrance rated


### Ordering and shipping details

Category	22642 - DISCONNECT SWITCHES - D10
Discount Schedule	T
GTIN	00785901878056
Nbr. of units in pkg.	1
Package weight(Lbs)	7.86 lb(US) (3.57 kg)
Returnability	No
Country of origin	MX

### Packing Units

Package 1 Height	3.70 in (9.398 cm)
Package 1 width	10.90 in (27.686 cm)
Package 1 Length	16.50 in (41.910 cm)

### Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
EU RoHS Directive	Not compliant
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>

### Contractual warranty

Warranty	18 months
----------	-----------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[D10S3H](#)