



Main

Range of Product	DA1
Product or Component Type	Thermistor probe
Device short name	DA1TT
Accessory / separate part category	Protection accessory
Quantity per Set	Set of 10
Ambient Air Temperature for Operation	284 °F (140 °C)

Complementary

[Ui] rated insulation voltage	2500 V
[Ue] rated operational voltage	<= 2.5 V
Resistance	250 Ohm per probe 25 °C
Insulation	Reinforced
Cable length	3.28 Ft (1 m) between probe and motor terminal plate 9.84 in (250 mm) between probes
Net Weight	0.02 lb(US) (0.01 kg)

Environment

Standards	IEC 60034-11 Mark A
-----------	---------------------

Ordering and shipping details





Category	22339-THERMISTER RELAY (LT3)
Discount Schedule	I11
GTIN	3389110531879
Nbr. of units in pkg.	1
Package weight(Lbs)	0.35 oz (10.0 g)
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	0.79 in (2 cm)
Package 1 width	3.54 in (9 cm)
Package 1 Length	5.12 in (13 cm)
Unit Type of Package 2	BAG
Number of Units in Package 2	10
Package 2 Weight	3.53 oz (100.0 g)
Package 2 Height	0.79 in (2 cm)
Package 2 width	3.54 in (9 cm)
Package 2 Length	5.12 in (13 cm)
Unit Type of Package 3	S01
Number of Units in Package 3	100
Package 3 Weight	2.70 lb(US) (1.225 kg)

Package 3 Height	5.91 in (15 cm)
Package 3 width	5.91 in (15 cm)
Package 3 Length	15.75 in (40 cm)

Offer Sustainability

California proposition 65	WARNING: Cancer - www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[DA1TT140](#)