

DF2CA04

NFC cartridge fuses, TeSys GS, cylindrical
10mm x 38mm, fuse type aM, 500VAC, 4A,
without striker



Main

Range of Product	TeSys fuse-disconnector
Product or Component Type	Cartridge fuse
Device short name	DF2
[Ue] rated operational voltage	500 V AC
Fuse size	10 x 38 mm
Fuse type	NFC
Quantity per Set	Set of 10

Complementary

Line Rated Current	4 A 500 V
Fuse curve	AM
Net Weight	0.02 lb(US) (0.01 kg)

Ordering and shipping details

Category	22621-IEC PANEL ACCESSORIES
Discount Schedule	I
GTIN	3389110501964
Nbr. of units in pkg.	1
Package weight(Lbs)	0.28 oz (8.0 g)
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	0.51 in (1.3 cm)
Package 1 width	1.57 in (4 cm)
Package 1 Length	4.25 in (10.8 cm)
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	2.82 oz (80.0 g)
Package 2 Height	0.51 in (1.3 cm)
Package 2 width	1.57 in (4 cm)
Package 2 Length	4.25 in (10.8 cm)
Unit Type of Package 3	S01
Number of Units in Package 3	720
Package 3 Weight	12.75 lb(US) (5.783 kg)
Package 3 Height	5.91 in (15 cm)
Package 3 width	5.91 in (15 cm)
Package 3 Length	15.75 in (40 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[DF2CA04](#)