



Main

| | |
|---------------------------|---|
| Range of Product | Linergy |
| Product or Component Type | Cable end |
| Cable end size | Medium |
| Standards | NF C 63-023 |
| Type of Packing | Bag |
| Quantity per Set | 10 sets of 100 |
| Cable cross section | 0.01 in ² (4 mm ²) |

Complementary

| | |
|------------------------|----------------------------------|
| Cable end type | Single conductor |
| Additional information | For additional marker tag holder |
| Color | Orange |
| Bezel material | Halogen-free plastic |
| Tube material | Copper ISO 1337 |
| Number of cables | 1 |
| AWG Gauge | AWG 12 |
| Bezel size | Ø 5.4 mm |
| Tube diameter | 0.13 in (3.2 mm) |
| Length | 0.79 in (20 mm) |
| Tube length | 0.39 in (10 mm) |
| CAD overall depth | 0.79 in (20 mm) |
| Net Weight | 0.66 lb(US) (0.3 kg) |

Environment

| | |
|---------------------------------------|----------------------------|
| Product Certifications | UL |
| Ambient Air Temperature for Operation | -4...221 °F (-20...105 °C) |

Ordering and shipping details

| | |
|-----------------------|-----------------------------|
| Category | 22621-IEC PANEL ACCESSORIES |
| Discount Schedule | I |
| GTIN | 3389110535679 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 0.01 oz (0.3 g) |
| Returnability | No |
| Country of origin | DE |

Packing Units

| | |
|------------------------------|------------------|
| Unit Type of Package 1 | PCE |
| Package 1 Height | 0.16 in (0.4 cm) |
| Package 1 width | 0.16 in (0.4 cm) |
| Package 1 Length | 0.55 in (1.4 cm) |
| Unit Type of Package 2 | BAG |
| Number of Units in Package 2 | 100 |

| | |
|------------------------------|--------------------|
| Package 2 Weight | 1.06 oz (30.0 g) |
| Package 2 Height | 0.79 in (2 cm) |
| Package 2 width | 2.36 in (6 cm) |
| Package 2 Length | 2.36 in (6 cm) |
| Unit Type of Package 3 | BB1 |
| Number of Units in Package 3 | 1000 |
| Package 3 Weight | 11.08 oz (314.0 g) |
| Package 3 Height | 1.77 in (4.5 cm) |
| Package 3 width | 4.33 in (11 cm) |
| Package 3 Length | 10.24 in (26 cm) |

Offer Sustainability

| | |
|-----------------------------|--|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |
| Halogen content performance | Halogen free product |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[DZ5CA042](#)