



Main

Range of Product	Linergy
Product or Component Type	Cable end
Cable end size	Medium
Standards	DIN 46228-1
Type of Packing	Individual bag
Quantity per Set	Set of 100
Cable cross section	0.02 in ² (10 mm ²)

Complementary

Cable end type	Single conductor
Additional information	Non-insulated
Bezel material	Halogen-free plastic
Tube material	Copper ISO 1337
Number of cables	1
AWG Gauge	AWG 8
Bezel size	Ø 5.8 mm
Tube diameter	0.18 in (4.5 mm)
Length	0.71 in (18 mm)
Tube length	0.71 in (18 mm)

Environment

Ambient Air Temperature for Operation	-4...221 °F (-20...105 °C)
---------------------------------------	----------------------------

Ordering and shipping details

Category	22621-IEC PANEL ACCESSORIES
Discount Schedule	I
GTIN	3389110537055
Nbr. of units in pkg.	1
Package weight(Lbs)	0.00 oz (0.1 g)
Returnability	No
Country of origin	DE

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	0.16 in (0.4 cm)
Package 1 width	0.16 in (0.4 cm)
Package 1 Length	0.55 in (1.4 cm)
Unit Type of Package 2	BAG
Number of Units in Package 2	100
Package 2 Weight	1.69 oz (48.0 g)
Package 2 Height	1.18 in (3 cm)
Package 2 width	1.77 in (4.5 cm)
Package 2 Length	4.92 in (12.5 cm)

Unit Type of Package 3	S02
Number of Units in Package 3	7000
Package 3 Weight	8.20 lb(US) (3.72 kg)
Package 3 Height	5.91 in (15 cm)
Package 3 width	11.81 in (30 cm)
Package 3 Length	15.75 in (40 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Halogen content performance	Halogen free plastic parts product

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[DZ5CE100](#)