



Main

Range of product	Harmony Modular iPC
Product or component type	Flat screen
Terminal type	Touchscreen display

Complementary

Device mounting	Flush
Local signalling	Status LED
View angle horizontal x vertical	140 x 115°
Contrast ratio	500:1
Touchscreen resolution	2048 x 2048
Function available	Operate with water on screen
[Us] rated supply voltage	24 V DC power supply 100...240 V AC power supply 47...63 Hz
Supply voltage limits	18...36 V DC
Power consumption in W	42.6 W (typical) with Box PC HMIBMP 58.65 W (maximum) with Box PC HMIBMP 37.4 W (typical) with Box PC HMIBMU 53.65 W (maximum) with Box PC HMIBMU
Display size	12.1 inch
Display type	Colour TFT LCD LED
Display resolution	1280 x 800 pixels WXGA
Display colour	16777216 colors
Luminance	300 Cd/M²
Backlight lifespan	50000 hours at 25 °C
Touch panel	Multi-touch projected capacitive technology (PCT)
Type of installation	Indoor installation
Inrush current	8.9 A
Width	488.3 Mm
Height	309 Mm
Depth	28 Mm enclosure: 7 Mm
Product weight	2.25 Kg

Environment

IP degree of protection	IP66
NEMA degree of protection	NEMA 4X
Standards	Class I division 2 CSA C22.2 No 213 CSA C22.2 No 142 UL 6110-2-201 Class I division 2 ANSI/ISA 12-12-01
Product certifications	IEC-Ex EAC CE C-Tick
Ambient air temperature for operation	0...55 °C
Ambient air temperature for storage	-30...70 °C
Pollution degree	2
Relative humidity	10...95 % non-condensing
Operating altitude	2000 m
Vibration resistance	1 gn (f = 5...500 Hz) HDD 2 gn (f = 5...500 Hz) SSD 2 gn (f = 5...500 Hz) Cfast card

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	4.13 Kg
Package 1 Height	47 Cm
Package 1 width	25.5 Cm
Package 1 Length	45 Cm
Unit Type of Package 2	CAR
Number of Units in Package 2	1
Package 2 Weight	4.25 Kg
Package 2 Height	45 Cm
Package 2 width	24.5 Cm
Package 2 Length	43 Cm
Unit Type of Package 3	P12
Number of Units in Package 3	6
Package 3 Weight	39.78 Kg
Package 3 Height	65 Cm
Package 3 width	80 Cm
Package 3 Length	120 Cm

Offer Sustainability

REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Product Life Status : **Commercialised**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[HMIDM6521](#)