

HMIDT75XFH

EXtreme touchscreen panel, Harmony GTUX, 15 W Display full coated

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 3950.00 USD



Main

Range of product	Harmony GTUX
Product or Component Type	EXtreme touchscreen panel
Terminal type	Touchscreen display

Complementary

Pixel resolution	1366 x 768
Touchscreen resolution	1024 x 1024
[Us] rated supply voltage	12...24 V DC power supply
Supply voltage limits	10.8...28.8 V
Power Consumption in W	12.5 W
Display size	15.6 inch
Display type	Colour TFT LCD
Display Resolution	1366 x 768 pixels FWXGA
Display colour	262144 colors
Luminance	92.90 Fc (1000 cd/m²)
Backlight lifespan	50000 hours
Touch panel	Single touch analogue resistive
Type of Installation	Outdoor
Type of cooling	Natural convection
Inrush current	30 A
Environmental characteristic	3C3 UV resistant
Cut-out dimensions	394 (+ 1/- 0) x 250 (+ 1/- 0) mm
Width	16.06 In (408 mm)
Height	10.39 In (264 mm)
Depth	2.68 In (68 mm)
Product Weight	10.58 Lb(US) (4.8 kg)

Environment

IP degree of protection	IP66f IP67f Front panel Type 4X
Standards	UL 508 ANSI/ISA 12-12-01 Class I division 2 CSA C22.2 No 213 CSA C22.2 No 142 IEC 61132-2
Product Certifications	KC CE RCM cULus
Ambient air temperature for operation	-4...140 °F (-20...60 °C) EN 61131-2
Ambient air temperature for storage	-4...140 °F (-20...60 °C)
Pollution degree	2
Relative Humidity	10...90 % non-condensing
Operating altitude	6561.68 ft (2000 m)
Vibration resistance	3.5 mm 5...9 Hz) EN/IEC 61131-2 9.8 m/s² 9...150 Hz) EN/IEC 61131-2
Shock resistance	147 m/s² EN/IEC 61131-2
Electromagnetic compatibility	Electrostatic discharge immunity testlevel 3 EN/IEC 61000-4-2
Environmental characteristic	3C3 UV resistant

Ordering and shipping details

Category	22567 - MAGELIS HMI GTU
Discount Schedule	MC2
GTIN	3606481572943
Nbr. of units in pkg.	1
Package weight(Lbs)	13.80 Lb(US) (6.261 kg)
Returnability	No

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	16.69 In (42.4 cm)
Package 1 width	6.89 In (17.5 cm)
Package 1 Length	20.75 In (52.7 cm)

Product Life Status : **Commercialised**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[HMIDT75XFH](#)