



Main

Range of Product	Harmony iPC
Product or Component Type	External power supply module
Accessory / separate part category	Electrical accessory

Complementary

Accessory / separate part destination	HMIDAD Harmony iPC HMIPSP S-Panel PC performance HMIPSO S-Panel PC
Input voltage	90...260 V AC 47...63 Hz
Input current	1600 mA 100 V AC
Output Voltage	24 V DC
Line Rated Current	2.62 A
Inrush current	70 A 230 V AC

Environment

Ambient air temperature for operation	32...158 °F (0...70 °C)
Ambient Air Temperature for Storage	-40...185 °F (-40...85 °C)
Relative Humidity	0...95 % non-condensing
Product Certifications	CE CSA 60950 CULus UL 60950

Ordering and shipping details

Category	22575-MAGELIS MC3
Discount Schedule	MC3
GTIN	3606480853784
Nbr. of units in pkg.	1
Package weight(Lbs)	21.16 oz (600.0 g)
Returnability	No
Country of origin	TW

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.36 in (3.45 cm)
Package 1 width	2.05 in (5.2 cm)
Package 1 Length	4.65 in (11.8 cm)
Unit Type of Package 2	CAR
Number of Units in Package 2	1
Package 2 Weight	2.43 lb(US) (1.1 kg)

Package 2 Height	5.91 in (15 cm)
Package 2 width	9.25 in (23.5 cm)
Package 2 Length	14.76 in (37.5 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[HMIYPSOMAC1](#)