



### Main

|                           |                         |
|---------------------------|-------------------------|
| Range of product          | Harmony 9001SK          |
| Product or component type | Selector switch         |
| Device short name         | 9001SK                  |
| Type of operator          | To centre spring return |
| Operator profile          | Green gloved hand knob  |

### Complementary

|                               |                          |
|-------------------------------|--------------------------|
| Bezel material                | Plastic                  |
| Mounting diameter             | 1.18 in (30 mm)          |
| Net weight                    | 0.13 lb(US) (0.059 kg)   |
| Shape of signaling unit head  | Round                    |
| Operator position information | 3 positions              |
| Contacts type and composition | Without contact block    |
| Mechanical durability         | 500000 cycles            |
| Light block supply            | Via integral transformer |
| Light source                  | incandescent             |
| Bulb base                     | BA 9s                    |
| [Us] rated supply voltage     | 110...120 V AC 50/60 Hz  |
| Compatibility code            | 9001SK                   |

### Environment

|                                       |                                                                                                                |
|---------------------------------------|----------------------------------------------------------------------------------------------------------------|
| Protective treatment                  | TC                                                                                                             |
| Ambient air temperature for storage   | -40...158 °F (-40...70 °C)                                                                                     |
| Ambient air temperature for operation | -13...158 °F (-25...70 °C)                                                                                     |
| Electrical shock protection class     | Class II IEC 61140                                                                                             |
| IP degree of protection               | IP66 IEC 60529                                                                                                 |
| NEMA degree of protection             | NEMA 1<br>NEMA 12<br>NEMA 13<br>NEMA 2<br>NEMA 3<br>NEMA 3R<br>NEMA 4<br>NEMA 4X<br>NEMA 6                     |
| Standards                             | CSA C22.2 No 14<br>UL 508<br>JIS C 852<br>EN/IEC 60947-1<br>JIS C 4520<br>EN/IEC 60947-5-4<br>EN/IEC 60947-5-1 |
| Product certifications                | UL 508<br>NEMA                                                                                                 |
| Vibration resistance                  | 7 gn 2...500 Hz)IEC 60068-2-6                                                                                  |
| Shock resistance                      | 50 gn IEC 60068-2-27                                                                                           |

## Ordering and shipping details

|                       |                      |
|-----------------------|----------------------|
| Category              | 21429 - 9001 SK,SKY  |
| Discount Schedule     | CS1                  |
| GTIN                  | 00785901711490       |
| Nbr. of units in pkg. | 1                    |
| Package weight(Lbs)   | 0.5 lb(US) (0.23 kg) |
| Returnability         | No                   |
| Country of origin     | MX                   |

## Offer Sustainability

|                            |                                                                                                                                                                                                                                                                                             |
|----------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status   | Green Premium product                                                                                                                                                                                                                                                                       |
| California proposition 65  | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| REACH Regulation           | <a href="#">REACH Declaration</a>                                                                                                                                                                                                                                                           |
| REACH free of SVHC         | Yes                                                                                                                                                                                                                                                                                         |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>                                                                                                                                                                                              |
| Toxic heavy metal free     | Yes                                                                                                                                                                                                                                                                                         |
| Mercury free               | Yes                                                                                                                                                                                                                                                                                         |
| RoHS exemption information | <a href="#">Yes</a>                                                                                                                                                                                                                                                                         |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>                                                                                                                                                                                                                                                      |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>                                                                                                                                                                                                                                               |
| WEEE                       | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.                                                                                                                                                                |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[9001SK52J1FG](#)