



### Main

|                           |                   |
|---------------------------|-------------------|
| Range of product          | Harmony 9001SK    |
| Product or component type | Pilot light       |
| Device short name         | 9001SK            |
| Lens type                 | Fresnel plastic   |
| Light block supply        | Direct 48 V AC/DC |

### Complementary

|                                             |                                                                          |
|---------------------------------------------|--------------------------------------------------------------------------|
| Bezel material                              | Plastic                                                                  |
| Mounting diameter                           | 1.18 in (30 mm)                                                          |
| Shape of signaling unit head                | Round                                                                    |
| Cap/operator or lens colour                 | Yellow                                                                   |
| Light source                                | incandescent                                                             |
| Bulb base                                   | BA 9s                                                                    |
| [Us] rated supply voltage                   | 48 V AC/DC                                                               |
| Tightening torque                           | 7.08 lbf.in (0.8 N.m) EN/IEC 60947-1                                     |
| Shape of screw head                         | Cross slotted                                                            |
| Connections - terminals                     | Screw clamp terminals, 1 x 0.22...2 x 1.5 mm <sup>2</sup> EN/IEC 60947-1 |
| [Ith] conventional free air thermal current | 10 A                                                                     |
| Short-circuit protection                    | 10 A cartridge fuse EN/IEC 60947-5-1                                     |
| [Ui] rated insulation voltage               | 250 V 2)EN/IEC 60947-1                                                   |
| [Uimp] rated impulse withstand voltage      | 2.5 kV EN/IEC 60947-1                                                    |
| Operating position                          | Any position                                                             |
| CAD overall width                           | 2.13 in (54 mm)                                                          |
| CAD overall height                          | 2.76 in (70 mm)                                                          |
| CAD overall depth                           | 1.65 in (42 mm)                                                          |
| Net weight                                  | 0.40 lb(US) (0.181 kg)                                                   |

### Environment

|                                       |                                                                                  |
|---------------------------------------|----------------------------------------------------------------------------------|
| Electrical shock protection class     | Class II IEC 61140                                                               |
| Protective treatment                  | TC                                                                               |
| IP degree of protection               | IP66 IEC 60529                                                                   |
| NEMA degree of protection             | NEMA 1<br>NEMA 12<br>NEMA 13<br>NEMA 2<br>NEMA 3<br>NEMA 3R<br>NEMA 4<br>NEMA 4X |
| Vibration resistance                  | 7 gn 2...500 Hz)IEC 60068-2-6                                                    |
| Shock resistance                      | 50 gn IEC 60068-2-27                                                             |
| Ambient air temperature for operation | -13...158 °F (-25...70 °C)                                                       |
| Ambient air temperature for storage   | -40...158 °F (-40...70 °C)                                                       |

|                        |                                                                                                                                  |
|------------------------|----------------------------------------------------------------------------------------------------------------------------------|
| Standards              | UL 508<br>JIS C 852<br>JIS C8201-5-1<br>CSA C22.2 No 14<br>EN/IEC 60947-5-1<br>EN/IEC 60947-5-4<br>EN/IEC 60947-1<br>JIS C8201-1 |
| Product certifications | UL 508<br>NEMA                                                                                                                   |

### Ordering and shipping details

|                       |                      |
|-----------------------|----------------------|
| Category              | 21429 - 9001 SK,SKY  |
| Discount Schedule     | CS1                  |
| GTIN                  | 00785901842590       |
| Nbr. of units in pkg. | 1                    |
| Package weight(Lbs)   | 0.5 lb(US) (0.23 kg) |
| Returnability         | No                   |
| Country of origin     | MX                   |

### Offer Sustainability

|                            |                                                                                                                                                                                                                                                                                             |
|----------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status   | Green Premium product                                                                                                                                                                                                                                                                       |
| California proposition 65  | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| REACH Regulation           | <a href="#">REACH Declaration</a>                                                                                                                                                                                                                                                           |
| REACH free of SVHC         | Yes                                                                                                                                                                                                                                                                                         |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>                                                                                                                                                                                              |
| Toxic heavy metal free     | Yes                                                                                                                                                                                                                                                                                         |
| Mercury free               | Yes                                                                                                                                                                                                                                                                                         |
| RoHS exemption information | <a href="#">Yes</a>                                                                                                                                                                                                                                                                         |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>                                                                                                                                                                                                                                                      |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>                                                                                                                                                                                                                                               |
| WEEE                       | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.                                                                                                                                                                |

### Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[9001SKP36A31](#)