


Product data sheet

Characteristics

XVS96BMBN

Electronic alarm, black, NPN, mounting support
DIN 96, 0...96 dB, 16 tones, 4 channels, 12...
24 V AC/DC



Main

Range of product	Harmony XVS
Product or component type	Electronic alarm
Device short name	XVS

Complementary

Color	Black
Material	PC (polycarbonate) terminal cover PC (polycarbonate)/ABS (acrylonitrile butadiene-styrene) body
Net Weight	0.88 lb(US) (0.4 kg)
Marking	CE
Oversupply category	Class II EN/IEC 61140
Mounting support	96 mm DIN rail
[Us] rated supply voltage	12...24 V DC
[Uimp] rated impulse withstand voltage	0.8 kV
Current consumption	250 mA 12 V 292 mA 12 V 292 mA 24 V 354 mA 24 V
Clamping connection capacity	<= 1 x 1.5 mm ²
Maximum Width	3.78 in (96 mm)
Height	3.78 in (96 mm)
Depth	2.29 in (58.1 mm)

Environment

Discrete output type	NPN
Signalling type	16 tones alarm
Standards	EN/IEC 60947-5-1 EN/IEC 60947-1
Protective treatment	TC
Ambient air temperature for storage	-31...158 °F (-35...70 °C)
Ambient air temperature for operation	-4...122 °F (-20...50 °C)
IP degree of protection	Panel mounted IP54 EN/IEC 60529
Noise level	0...96 dB continuous or intermittent tone)1 m

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or operator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Ordering and shipping details

Category	22617 - XVC TOWER LIGHTS
Discount Schedule	XV
GTIN	03606480072017
Nbr. of units in pkg.	1
Package weight(Lbs)	0.4 lb(US) (0.18 kg)
Returnability	No
Country of origin	JP

Packing Units

Package 1 Height	1.350 dm
Package 1 width	1.410 dm
Package 1 Length	1.410 dm

Offer Sustainability


Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information

Contractual warranty

Warranty	18 months
----------	-----------

Electronic Alarm

Dimensions



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[XVS96BMBN](#)