



Main

Range of Product	Hyde Park
Sensor Type	Ultrasonic sensor
Series name	Superprox +
Device short name	SC656
Sensor design	Flat form
[Sn] nominal sensing distance	10.00 in (254 mm)
Type of sensing window	Configurable
Material	Plastic
Enclosure Material	ULTEM
Front material	Silicone rubber
Type of output signal	Analog
Wiring Technique	4-wire
[Us] rated supply voltage	15...24 V DC overload and short-circuit protection
Supply voltage limits	13...28 V DC
Analogue output range	4...20 mA configurable
Electrical connection	1 male connector M12 4 pins
Product Specific Application	Analog output

Complementary

Blind zone	2.01 in (51 mm)
Transmission frequency	500 kHz
Beam angle	10 °
Minimum size of detected object	Cylinder diameter 1.59 mm - up to 76.2 mm sensing distance
Current Consumption	50 mA
Maximum switching current	100 mA reverse polarity protection
Height	0.64 in (16.25 mm)
Width	1.18 in (30 mm)
Depth	0.64 in (16.25 mm)
Length	3.32 in (84.32 mm)
Net Weight	0.10 lb(US) (0.045 kg)

Environment

Product Certifications	UL
Marking	CE
NEMA degree of protection	NEMA 4X indoor use only)
IP degree of protection	IP67
Ambient air temperature for operation	32...140 °F (0...60 °C)
Ambient Air Temperature for Storage	-40...212 °F (-40...100 °C)
Relative humidity	100 % without condensation
Vibration resistance	+/-1 mm 10...55 Hz)IEC 60068-2-6
Shock resistance	30 gn in all 3 axes 11 ms IEC 60068-2-27
Resistance to electromagnetic fields	9.14 V/m (10 V/m) level 3 IEC 61000-4-3
Resistance to fast transients	1 kV level 3 IEC 61000-4-4

Ordering and shipping details

Category	22490 - SENSORS-ULTRASONIC (XX5,6)
Discount Schedule	DS2
GTIN	03389119086622
Nbr. of units in pkg.	1
Package weight(Lbs)	0.2 lb(US) (0.09 kg)
Returnability	No
Country of origin	US

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Not applicable, out of EU RoHS legal scope

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[SC656ABC0AFFP](#)