



Main

Range of Product	Hyde Park
Sensor Type	Ultrasonic sensor
Series name	Superprox 600
Device short name	SM602
Sensor design	Cylindrical M18
[Sn] nominal sensing distance	12.01 in (305 mm)
Type of sensing window	Fixed
Material	Plastic
Enclosure Material	ULTEM
Front material	Silicone rubber
Type of output signal	Discrete
Discrete output function	1 NO
ISO thread	M18 x 1
Wiring Technique	4-wire

Resistance to electromagnetic fields	9.14 V/m (10 V/m) level 3 IEC 61000-4-3
Resistance to fast transients	1 kV level 3 IEC 61000-4-4

Ordering and shipping details

Category	22490 - SENSORS-ULTRASONIC (XX5,6)
Discount Schedule	DS2
GTIN	03389119099257
Nbr. of units in pkg.	1
Package weight(Lbs)	0.37 lb(US) (0.17 kg)
Returnability	No
Country of origin	US

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Not applicable, out of EU RoHS legal scope

Contractual warranty

||
||
||

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[SM602AH3213](#)