



**Main**

Range of Product	Hyde Park
Sensor Type	Ultrasonic sensor
Series name	Superprox 600
Device short name	SM606
Sensor design	Cylindrical M18
[Sn] nominal sensing distance	4.00 in (101.6 mm)
Type of sensing window	Fixed
Material	Plastic
Enclosure Material	ULTEM
Front material	Silicone rubber
Type of output signal	Analog
ISO thread	M18 x 1
Wiring Technique	4-wire
[Us] rated supply voltage	15...24 V DC overload and short-circuit protection
Supply voltage limits	13...28 V DC
Analogue output range	0...10 V direct
Electrical connection	Cable, 9.84 ft (3 m)
Product Specific Application	Analog output

**Complementary**

[Sd] sensing range	1.25...4.00 in (31.7...101.6 mm)
Blind zone	0.75 in (19 mm)
Transmission frequency	500 kHz
Beam angle	10 °
Minimum size of detected object	Cylinder diameter 1.59 mm - up to 63.5 mm sensing distance
Current Consumption	50 mA
Maximum switching current	100 mA reverse polarity protection
Height	0.71 in (18 mm)
Width	0.71 in (18 mm)
Depth	0.71 in (18 mm)
Length	2.55 in (64.77 mm)
Net Weight	0.37 lb (US) (0.17 kg)

**Environment**

Product Certifications	UL
Marking	CE
NEMA degree of protection	NEMA 4X indoor use only
IP degree of protection	IP67
Ambient air temperature for operation	32...140 °F (0...60 °C)
Ambient Air Temperature for Storage	-40...212 °F (-40...100 °C)
Relative humidity	100 % without condensation
Vibration resistance	+/-1 mm 10...55 Hz) IEC 60068-2-6
Shock resistance	30 gn in all 3 axes 11 ms IEC 60068-2-27

Resistance to electromagnetic fields	9.14 V/m (10 V/m) level 3 IEC 61000-4-3
Resistance to fast transients	1 kV level 3 IEC 61000-4-4

### Ordering and shipping details

Category	22490 - SENSORS-ULTRASONIC (XX5,6)
Discount Schedule	DS2
GTIN	03389119100632
Nbr. of units in pkg.	1
Package weight(Lbs)	0.37 lb(US) (0.17 kg)
Returnability	No
Country of origin	US

### Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisobutyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	 Yes
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	 <a href="#">End Of Life Information</a>

### Contractual warranty

Warranty	18 months
----------	-----------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[SM606A44401](#)