

LE1D098B62OG70

FULL-VOLTAGE NON-REVERSING IEC STARTER FUSIBLE DISCONNECT 30A TYPE 1



Main

Product or component type	Full voltage starter
Range of product	Instakits
Starter Type	Non reversing
Disconnect Type	Fusible disconnect

Complementary

Control Circuit Voltage	120 V AC 50/60 Hz
Current Rating	9 A
Horsepower Rating	0.3 Hp at 120 V AC, 1 phase 1 Hp 240 V AC, 1 phase 2 Hp 208 V AC, 3 phase 2 Hp 230 V AC, 3 phase 5 Hp 460 V AC, 3 phase 7.5 hp 575 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Auxiliary Contacts	1 NO + 1 NC
Protection type	Switch-disconnector fuse 30 A
Location of connection	Line

Environment

Product certifications	CSA IEC UL
Enclosure Type	NEMA 1 steel

Ordering and shipping details

Category	22313 - CTRS,D-LINE,ENCL (METAL)
Discount Schedule	I11
GTIN	00785901297956
Package weight(Lbs)	37.6 lb(US) (17.06 kg)
Returnability	Yes
Country of origin	MX

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[LE1D098B62OG70](#)