

# LE1D128B62OG70

## FULL-VOLTAGE NON-REVERSING IEC STARTER FUSIBLE DISCONNECT 30A TYPE 1



### Main

|                           |                      |
|---------------------------|----------------------|
| Product or component type | Full voltage starter |
| Range of product          | Instakits            |
| Starter Type              | Non reversing        |
| Disconnect Type           | Fusible disconnect   |

### Complementary

|                         |                                                                                                                                                               |
|-------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Control Circuit Voltage | 120 V AC 50/60 Hz                                                                                                                                             |
| Current Rating          | 12 A                                                                                                                                                          |
| Horsepower Rating       | 0.5 Hp 120 V AC, 1 phase<br>2 Hp 240 V AC, 1 phase<br>3 Hp 208 V AC, 3 phase<br>3 Hp 230 V AC, 3 phase<br>7.5 Hp 460 V AC, 3 phase<br>10 hp 575 V AC, 3 phase |
| Maximum Voltage Rating  | 600 V AC                                                                                                                                                      |
| Auxiliary Contacts      | 1 NO + 1 NC                                                                                                                                                   |
| Protection type         | Switch-disconnector fuse 30 A                                                                                                                                 |
| Location of connection  | Line                                                                                                                                                          |

### Environment

|                        |                  |
|------------------------|------------------|
| Product certifications | CSA<br>IEC<br>UL |
| Enclosure Type         | NEMA 1 steel     |

### Ordering and shipping details

|                     |                                  |
|---------------------|----------------------------------|
| Category            | 22313 - CTRS,D-LINE,ENCL (METAL) |
| Discount Schedule   | I11                              |
| GTIN                | 00785901408208                   |
| Package weight(Lbs) | 1 lb(US) (0.45 kg)               |
| Returnability       | Yes                              |
| Country of origin   | MX                               |

## Offer Sustainability

|                            |                                                                                                                                                                                                                                                           |
|----------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status   | Green Premium product                                                                                                                                                                                                                                     |
| California proposition 65  | WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| REACH Regulation           | <a href="#">REACH Declaration</a>                                                                                                                                                                                                                         |
| REACH free of SVHC         | Yes                                                                                                                                                                                                                                                       |
| EU RoHS Directive          | Compliant <a href="#">EU RoHS Declaration</a>                                                                                                                                                                                                             |
| Toxic heavy metal free     | Yes                                                                                                                                                                                                                                                       |
| Mercury free               | Yes                                                                                                                                                                                                                                                       |
| RoHS exemption information | <a href="#">Yes</a>                                                                                                                                                                                                                                       |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>                                                                                                                                                                                                                    |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>                                                                                                                                                                                                             |
| PVC free                   | Yes                                                                                                                                                                                                                                                       |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[LE1D128B62OG70](#)