



### Main

|                           |                      |
|---------------------------|----------------------|
| Product or Component Type | Full voltage starter |
| Range of Product          | Instakits            |
| Starter Type              | Non reversing        |

### Complementary

|                         |                                                                                                                                                              |
|-------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Control Circuit Voltage | 120 V AC 50/60 Hz                                                                                                                                            |
| Current Rating          | 32 A AC-3<br>50 A AC-1                                                                                                                                       |
| Horsepower Rating       | 2 Hp 120 V AC, 1 phase<br>5 Hp 240 V AC, 1 phase<br>10 Hp 208 V AC, 3 phase<br>10 Hp 230 V AC, 3 phase<br>20 Hp 460 V AC, 3 phase<br>25 hp 575 V AC, 3 phase |
| Maximum Voltage Rating  | 600 V AC                                                                                                                                                     |
| Auxiliary Contacts      | 1 NO + 1 NC                                                                                                                                                  |
| Location of connection  | Line                                                                                                                                                         |
| Height                  | 12.05 in (306 mm)                                                                                                                                            |
| Depth                   | 7.91 in (201 mm)                                                                                                                                             |
| Width                   | 6.77 in (172 mm)                                                                                                                                             |

### Environment

|                        |                             |
|------------------------|-----------------------------|
| Product Certifications | IEC<br>CSA<br>UL            |
| Enclosure Type         | NEMA 12 painted sheet steel |

### Ordering and shipping details

|                       |                                  |
|-----------------------|----------------------------------|
| Category              | 22313 - CTRS,D-LINE,ENCL (METAL) |
| Discount Schedule     | I11                              |
| GTIN                  | 785901805915                     |
| Nbr. of units in pkg. | 1                                |
| Package weight(Lbs)   | 48.00 lb(US) (21.772 kg)         |
| Returnability         | No                               |
| Country of origin     | MX                               |

### Packing Units

|                        |                    |
|------------------------|--------------------|
| Unit Type of Package 1 | PCE                |
| Package 1 Height       | 12.05 in (30.6 cm) |
| Package 1 width        | 6.77 in (17.2 cm)  |
| Package 1 Length       | 7.91 in (20.1 cm)  |

## Offer Sustainability

|                            |                                                                                                                                                                                                                                                           |
|----------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status   | Green Premium product                                                                                                                                                                                                                                     |
| California proposition 65  | WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| REACH Regulation           | <a href="#">REACH Declaration</a>                                                                                                                                                                                                                         |
| REACH free of SVHC         | Yes                                                                                                                                                                                                                                                       |
| EU RoHS Directive          | Compliant <a href="#">EU RoHS Declaration</a>                                                                                                                                                                                                             |
| Toxic heavy metal free     | Yes                                                                                                                                                                                                                                                       |
| Mercury free               | Yes                                                                                                                                                                                                                                                       |
| RoHS exemption information | <a href="#">Yes</a>                                                                                                                                                                                                                                       |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>                                                                                                                                                                                                                    |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>                                                                                                                                                                                                             |
| WEEE                       | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.                                                                                                                              |
| PVC free                   | Yes                                                                                                                                                                                                                                                       |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[LE1D323A72OG70](#)