



### Overview

Lead time	Usually in Stock
-----------	------------------

### General

Provided equipment	Battery modules ship installed CD with software Removable heavy duty 12 gauge input power cord Removable support feet User Manual USB cable
--------------------	--

### Physical

Cable length	10 ft (3.05 m)
Color	Black
Depth	17.99 in (45.7 cm)
Height	5.24 in (13.3 cm)
Product Weight	43.39 lb(US) (19.68 kg)
Width	17.01 in (43.2 cm)

### Input

Input Frequency	50/60 Hz +/- 3 Hz auto-sensing
Plug standard	NEMA 5-15P
Efficiency at full load	90...140 V
Maximum Input Current per Phase	12 A
Switching current capacity	15 A
Nominal Input Voltage	120 V

### Output

Kw Rating	600 W
Max Configurable Power (Watts)	600 W
Topology	Line Interactive
Waveform Type	Stepped approximation to a sinewave
Nb of power socket outlets	12 NEMA 5-15R
Output voltage	120 V

## Conformance

Product Certifications	CSA
Standards	FCC Part 15 class B FCC part 68 UL 1778 UL 498
Equipment protection policy	Lifetime : \$750000

## Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Relative Humidity	5...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

## Batteries & Runtime

Battery Type	Lead-Acid battery
Included Battery Modules	1
Battery Slots Empty	0
Typical recharge time	16 h
Liquid Electrolyte Value	0

## Communications & Management

Control panel	Multi-function LCD status and control console
Audible Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays

## Surge Protection and Filtering

Surge energy rating	3200 J
Filtering	Full time multi-pole noise filtering : 0.7% IEEE surge let-through : zero clamping response time : m
Data line protection	RJ11 Modem/Fax protection (two wire single line) Cable modem/video protection Co-axial Video / Cable protection



## Ordering and shipping details

Category	11309 - APC RESALE PRODUCTS
GTIN	00731304235965
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	No
Country of origin	PH

## Packing Units

Package 1 Height	12.99 in (33 cm)
Package 1 width	21.50 in (54.6 cm)
Package 1 Length	24.02 in (61 cm)
SCC14	107313040
Number of Units in Package 2	1
Number of Units in Package 3	12

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	 <a href="#">Yes</a>
Optimized Energy Efficiency	Energy efficient product

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[J10BLK](#)