



Overview

Lead time	Usually in Stock
-----------	------------------



General

Provided equipment	CD with software User Manual
--------------------	---------------------------------

Physical

Color	Black
Depth	16.00 in (40.64 cm)
Height	3.84 in (9.76 cm)
Product Weight	30.86 lb(US) (14 kg)
Width	17.00 in (43.18 cm)

Input

Plug standard	NEMA 5-15P
Nominal Input Voltage	120 V

Output

Kw Rating	865 W
Max Configurable Power (Watts)	865 W
Waveform Type	Stepped approximation to a sine wave
Nb of power socket outlets	6 NEMA 5-15R 2 NEMA 5-15R surge
Output voltage	120 V

Conformance

Standards	FCC Part 15 class B UL 1778
Equipment protection policy	Lifetime : \$350000

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5...104 °F (-15...40 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...10000 ft (0.00...3048.00 m)
Acoustic level	45 dBA

Batteries & Runtime

Battery Type	Lead-Acid battery
Included Battery Modules	1
Battery Slots Empty	0
Typical recharge time	16 h
Liquid Electrolyte Value	0

Surge Protection and Filtering

Surge energy rating	345 J
---------------------	-------



Ordering and shipping details

Category	11309 - APC RESALE PRODUCTS
GTIN	00731304277699
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	No
Country of origin	PH

Packing Units

Package 1 Height	8.07 in (20.51 cm)
Package 1 width	22.00 in (55.88 cm)
Package 1 Length	21.24 in (53.94 cm)
SCC14	10731304277696
Number of Units in Package 2	2
Package 2 Weight	74.93 lb(US) (33.99 kg)
Package 2 Height	17 in (431.80 mm)
Package 2 width	23 in (584.20 mm)
Package 2 Length	22 in (558.80 mm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
Optimized Energy Efficiency	Energy efficient product

Contractual warranty

Warranty	3 years repair or replace
----------	---------------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[J35B](#)