



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Main Input Voltage	120 V
Main Output Voltage	120 V
Kw Rating	1200 W
Rated power in VA	1200 VA
Plug standard	NEMA 5-15P
Cable length	6.5 ft (1.98 m)
Number of cables	1
Provided equipment	User Manual

Physical

Color	Beige
Height	4.57 in (11.6 cm)
Width	8.43 in (21.4 cm)
Depth	5.55 in (14.1 cm)
Net Weight	9.70 lb(US) (4.4 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable
Two post mountable	0
USB compatible	No

Input

Input Frequency	50/60 Hz
-----------------	----------

Output

Max Configurable Power (Watts)	1200 W
--------------------------------	--------

Conformance

Product Certifications	CUL Listed NOM
Standards	FCC Part 15 class B UL 1012
Equipment protection policy	Lifetime : \$25000

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Relative Humidity	5...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	5...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Batteries & Runtime

Included Battery Modules	0
Battery Slots Empty	0

Surge Protection and Filtering

Surge energy rating	680 J
---------------------	-------

Ordering and shipping details

GTIN	731304197911
Package weight(Lbs)	10.36 lb(US) (4.7 kg)

Packing Units

Package 1 Height	6.89 in (17.5 cm)
Package 1 width	10.75 in (27.3 cm)
Package 1 Length	8.15 in (20.7 cm)
SCC14	10731304197918
Number of Units in Package 2	4
Package 2 Weight	43 lb(US) (19.50 kg)
Package 2 Length	16.73 in (424.94 mm)
Number of Units in Package 3	64

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Under investigation

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[LE1200](#)