



Overview

Lead time	Usually in Stock
-----------	------------------

General

Provided equipment	User manual
--------------------	-------------

Physical

Cable length	1.98 M
Colour	Beige
Depth	14.1 Cm
Height	11.6 Cm
Mounting preference	No preference
Product weight	3.3 Kg
Mounting mode	Not rack-mountable
Width	21.4 Cm

Input

Network frequency	50/60 Hz
Plug standard	NEMA 5-15P
Number of cables	1
Input voltage	120 V

Output

Rated power in W	600 W
Maximum configurable power in W	600 W
Output voltage	120 V
Rated power in VA	600 VA

Conformance

Product certifications	CUL listed NOM
Standards	FCC part 15 class B UL 1012
Equipment protection policy	Lifetime : \$25000

Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	5...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-25...65 °C
Storage Relative Humidity	5...95 %
Storage altitude	0.00...15240.00 M

Batteries & Runtime

Number of battery filled slots	0
Number of battery free slots	0
Liquid value	0

Surge Protection and Filtering

Surge energy rate	680 J
-------------------	-------

Packing Units

Package 1 Weight	3.6 Kg
Package 1 Height	17.5 Cm
Package 1 width	27.3 Cm
Package 1 Length	20.7 Cm
SCC14	10731304197925
Number of Units in Package 2	4
Package 2 Weight	15.42 Kg
Package 2 Length	424.94 Mm
Number of Units in Package 3	64

Offer Sustainability

EU RoHS Directive	Under investigation
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Product Life Status :	Commercialised
-----------------------	----------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[LE600](#)