



Main

Range	TeSys
Device short name	LU9G
Product or Component Type	Profibus DP power supply module
Product Compatibility	LULC07

Complementary

[Us] rated supply voltage	24 V DC
Maximum current I _{rms}	1.5 A
Width	1.77 in (45 mm)
Height	6.69 in (170 mm)
Depth	2.56 in (65 mm)

Ordering and shipping details

Category	22399-TESYS U, ACCESSORIES
Discount Schedule	I11
GTIN	3389119409735
Nbr. of units in pkg.	1
Package weight(Lbs)	9.66 oz (274.0 g)
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.97 in (5 cm)
Package 1 width	3.54 in (9 cm)
Package 1 Length	8.07 in (20.5 cm)
Unit Type of Package 2	S03
Number of Units in Package 2	25
Package 2 Weight	16.55 lb(US) (7.506 kg)
Package 2 Height	11.81 in (30 cm)
Package 2 width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Compliant EU RoHS Declaration
China RoHS Regulation	China RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[LU9GC7](#)