



Main

Range	Linergy
Product name	HK
Product or Component Type	Plug outlet
Poles description	1P + N
[I _{th}] conventional free air thermal current	16 A
I ² t on activation	100000 A ² .s
Number of points	1
Number of cables	2 0.00 in ² (2.5 mm ²)
Cable length	0.66 ft (0.2 m)
Quantity per Set	Set of 6

Complementary

[Ui] rated insulation voltage	600 V CSA 600 V UL 690 V IEC 60439-1
Peak current	25 kA
Width	0.71 in (18 mm)
Height	1.81 in (46 mm)
Depth	1.50 in (38 mm)
Net Weight	0.08 lb(US) (0.035 kg)

Environment

Standards	IEC 60439
Product Certifications	DNV UL LROS (Lloyds register of shipping) CSA

Ordering and shipping details

Category	22623 - PANEL BUS (AK5)
Discount Schedule	I11
GTIN	3389110576801
Nbr. of units in pkg.	1
Package weight(Lbs)	0.99 oz (28 g)
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.57 in (4 cm)
Package 1 width	4.33 in (11 cm)
Package 1 Length	2.56 in (6.5 cm)
Unit Type of Package 2	BB1
Number of Units in Package 2	6
Package 2 Weight	8.25 oz (234 g)
Package 2 Height	5.35 in (13.6 cm)

Package 2 width	6.22 in (15.8 cm)
Package 2 Length	5.04 in (12.8 cm)
Unit Type of Package 3	S04
Number of Units in Package 3	96
Package 3 Weight	10.14 lb(US) (4.598 kg)
Package 3 Height	11.81 in (30 cm)
Package 3 width	15.75 in (40 cm)
Package 3 Length	23.62 in (60 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[AK5PC12](#)